



Rev. 10/2012

16619 Aldine Westfield Rd, Houston, TX 77032 USA Tel 832.467.9898 Fax 832.467.9897
 Website: www.FluidSystems.com

FSI Screens Part Numbers Conversion Chart

API RP 13C (ISO 13501)

					API RP 13 C Designation
New P/N	Old P/N	API No.	D100 (microns)	Conductance (kD/mm)	D100 (microns)
FLOMAX SQUARE LAYERED DE-BLINDING SCREENS					
FMD A20	FMD 024	20	793	18.38	>780.0 to 925.0
FMD A35	FMD 038	35	518	8.80	>462.5 to 550.0
FMD A40	FMD 040	40	432	7.95	>390.0 to 462.5
FMD A45	FMD 050	45	376	7.09	>327.5 to 390.0
FMD A50	FMD 060	50	319	5.99	>275.0 to 327.5
FMD A60	FMD 070	60	261	4.88	>231.0 to 275.0
FMD A70	FMD 084	70	221	3.78	>196.0 to 231.0
FMD A80	FMD 100	80	194	3.45	>165.0 to 196.0
FMD A100	FMD 110	100	163	3.11	>137.5 to 165.0
FMD A120	FMD 140	120	137	2.45	>116.5 to 137.5
FMD A140	FMD 175	140	116	1.94	>98.0 to 116.5
FMD A170	FMD 210	170	97	1.70	>82.5 to 98.0
FMD A200	FMD 250	200	82	1.36	>69.0 to 82.5
FMD A230	FMD 325	230	62	0.80	>58.0 to 69.0
FMD A270	FMD 400	270	51	0.55	>49.0 to 58.0
FMD A325	FMD 450	325	45	0.41	>41.5 to 49.0
FLOMAX RECTANGLE LAYERED DE-BLINDING SCREENS					
FMR A35	FMR 050	35	514	8.77	>462.5 to 550.0
FMR A40	FMR 060	40	418	7.24	>390.0 to 462.5
FMR A45	FMR 070	45	351	6.92	>327.5 to 390.0
FMR A50	FMR 080	50	315	5.81	>275.0 to 327.5
FMR A60	FMR 084	60	272	4.71	>231.0 to 275.0
FMR A70	FMR 110	70	202	3.55	>196.0 to 231.0
FMR A80	FMR 140	80	169	2.78	>165.0 to 196.0
FMR A100	FMR 150	100	164	2.47	>137.5 to 165.0
FMR A120	FMR 175	120	136	2.16	>116.5 to 137.5
FMR A140	FMR 210	140	114	1.85	>98.0 to 116.5
FMR A170	FMR 230	170	86	1.68	>82.5 to 98.0
FMR A200	FMR 250	200	82	1.68	>69.0 to 82.5
FMR A230	FMR 325	230	69	0.97	>58.0 to 69.0
FMR A270	FMR 400	270	49	0.78	>49.0 to 58.0
FMR A325	FMR 450	325	43	0.56	>41.5 to 49.0